















# DriSteem Steam Generation Product Comparison



## DriSteem Steam Dispersion Product Comparison

|   |                 | CAPACITY  | AIRFLOW                | INSULATED TUBES |
|---|-----------------|---|------------------------|-----------------|
| PRESSURIZED STEAM DISPERSION  | Framed Panel    |  Ultra-sorb® MP Steam dispersion panel<br>1247 kg/h                   | Horizontal             | Optional        |
|   |                 |  Ultra-sorb® LV Steam dispersion panel<br>1814 kg/h                   | Horizontal             | Optional        |
|   |                 |  Ultra-sorb® LH Steam dispersion panel<br>1482 kg/h                   | Horizontal<br>Vertical | Optional        |
|   |                 |  Ultra-sorb® XV Steam dispersion panel<br>1234 kg/h                   | Horizontal             | <b>Standard</b> |
|   | Steam Injection |  Mini-bank® humidifier<br>38 kg/h                                     | Horizontal<br>Vertical | Optional        |
|   |                 |  Single-tube humidifier<br>238 kg/h                                   | Horizontal<br>Vertical | Optional        |
|  Multiple-tube humidifier (with Maxi-bank® option)<br>1808 kg/h |                 | Horizontal<br>Vertical  | Optional               |                 |
| ATMOSPHERIC STEAM DISPERSION  | Framed Panel    |  Ultra-sorb® MP Steam dispersion panel<br>318 kg/h                    | Horizontal             | Optional        |
|   |                 |  Ultra-sorb® LV Steam dispersion panel<br>839 kg/h                   | Horizontal             | Optional        |
|   |                 |  Ultra-sorb® LH Steam dispersion panel<br>839 kg/h                  | Vertical               | Optional        |
|   |                 |  Ultra-sorb® XV (with STS® only) Steam dispersion panel<br>204 kg/h | Horizontal             | <b>Standard</b> |
|   | Unframed        |  Single dispersion tube<br>44 kg/h                                  | Horizontal<br>Vertical | Optional        |
|   |                 |  Rapid-sorb® dispersion tubes<br>953 kg/h                           | Horizontal<br>Vertical | Optional        |

Continuous product improvement is a policy of DriSteem; therefore, product features and specifications are subject to change without notice.

Product and corporate names used in this document may be trademarks or registered trademarks. They are used for explanation only without intent to infringe.

DriSteem, CRUV, DriCalc, GTS, Mini-bank, Rapid-sorb, STS, Ultra-sorb, Vapor-logic, Vapormist, and Vaporstream are registered trademarks of Research Products Corporation and are filed for trademark registration in Canada and the European community.

© 2020 Research Products Corporation  
Form No. ComparisonCharts\_Europe\_EN\_0420